

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250623

Luminaire Tested: **LD8B200D010 ER8B200930 8LBM0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250623  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B200D010 ER8B200930 8LBM0B  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11237.0 lumens  
Efficiency: N/A  
Efficacy: 50.3 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 223.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250623

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBM0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250623

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBM0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250623

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBM0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1280.6	11.4
10°-20°	2974.1	26.5
20°-30°	3773.1	33.6
30°-40°	2584.9	23.0
40°-50°	589.0	5.2
50°-60°	29.4	0.3
60°-70°	1.4	0.0
70°-80°	2.2	0.0
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8027.9	71.4
0°-40°	10612.8	94.4
0°-60°	11231.2	99.9
0°-90°	11237.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11237.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	14580	
5°	14081	###
15°	10556	2974
25°	8357	3773
35°	4176	2585
45°	635	589
55°	11	29
65°	6	1
75°	0	2
85°	0	2
90°	0	



TEST NUMBER: P250623

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBM0B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	14580.3
1°	14656.3
2°	14629.0
3°	14520.4
4°	14335.8
5°	14080.7
6°	13771.1
7°	13412.8
8°	13016.3
9°	12592.6
10°	12190.9
11°	11821.6
12°	11425.2
13°	11137.5
14°	10833.3
15°	10556.5
16°	10306.7
17°	10062.2
18°	9834.2
19°	9611.5
20°	9410.6
21°	9204.2
22°	8992.4
23°	8807.9
24°	8601.5
25°	8357.2
26°	8085.7
27°	7770.8
28°	7434.0
29°	7059.4
30°	6646.6
31°	6179.6
32°	5696.4
33°	5191.4
34°	4675.4
35°	4175.8
37.5°	2948.7
40°	1900.5
42.5°	1118.6
45°	635.4
47.5°	342.1
50°	173.8
52.5°	32.5
55°	10.9
57.5°	5.5



TEST NUMBER: P250623

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBM0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	0.0
62.5°	0.0
65°	5.5
67.5°	0.0
70°	0.0
72.5°	5.5
75°	0.0
77.5°	0.0
80°	5.5
82.5°	0.0
85°	0.0
87.5°	5.5
90°	0.0

(END OF REPORT)