

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250371

Luminaire Tested: **LD8B200D010 ER8B200930 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B200930 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13981.2 lumens
Efficiency: N/A
Efficacy: 62.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250371

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250371

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250371

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2005.5	14.3
10°-20°	4358.9	31.2
20°-30°	4679.5	33.5
30°-40°	2529.2	18.1
40°-50°	394.6	2.8
50°-60°	10.9	0.1
60°-70°	2.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11043.9	79.0
0°-40°	13573.1	97.1
0°-60°	13978.5	100.0
0°-90°	13981.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13981.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22340	
5°	21900	###
15°	15563	4359
25°	10373	4680
35°	3973	2529
45°	364	395
55°	0	11
65°	0	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250371

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBNOGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	22340.4
1°	22382.8
2°	22361.8
3°	22285.3
4°	22138.1
5°	21899.9
6°	21571.7
7°	21130.4
8°	20578.0
9°	19942.1
10°	19235.1
11°	18493.5
12°	17724.1
13°	16955.5
14°	16241.3
15°	15563.1
16°	14940.4
17°	14338.8
18°	13779.2
19°	13255.3
20°	12751.3
21°	12261.4
22°	11799.4
23°	11338.6
24°	10855.9
25°	10372.8
26°	9883.1
27°	9323.9
28°	8708.0
29°	8079.3
30°	7421.4
31°	6715.0
32°	6008.0
33°	5308.8
34°	4602.5
35°	3972.7
37.5°	2539.0
40°	1469.0
42.5°	783.7
45°	364.0
47.5°	196.3
50°	63.4
52.5°	7.2
55°	0.0
57.5°	7.2



TEST NUMBER: P250371

CATALOG NUMBER: LD8B200D010 ER8B200930 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	7.2
62.5°	0.0
65°	0.0
67.5°	7.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)