

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250427

Luminaire Tested: **LD8B200D010 ER8B200935 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B200935 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10490.0 lumens
Efficiency: N/A
Efficacy: 47.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250427

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P250427

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBN0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	516878
5°	508619
10°	451898
15°	372775
20°	313951
25°	264799
30°	198269
35°	112206
40°	44368
45°	11910
50°	2284
55°	0
60°	327
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250427

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBN0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1504.7	14.3
10°-20°	3270.4	31.2
20°-30°	3511.1	33.5
30°-40°	1897.6	18.1
40°-50°	296.1	2.8
50°-60°	8.1	0.1
60°-70°	2.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8286.2	79.0
0°-40°	10183.8	97.1
0°-60°	10488.0	100.0
0°-90°	10490.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10490.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16762	
5°	16431	###
15°	11677	3270
25°	7783	3511
35°	2981	1898
45°	273	296
55°	0	8
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250427

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBN0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	16762.0
1°	16793.8
2°	16778.0
3°	16720.6
4°	16610.2
5°	16431.4
6°	16185.2
7°	15854.1
8°	15439.6
9°	14962.6
10°	14432.1
11°	13875.6
12°	13298.4
13°	12721.6
14°	12185.8
15°	11676.9
16°	11209.8
17°	10758.4
18°	10338.5
19°	9945.4
20°	9567.2
21°	9199.7
22°	8853.1
23°	8507.3
24°	8145.1
25°	7782.7
26°	7415.3
27°	6995.7
28°	6533.6
29°	6061.9
30°	5568.3
31°	5038.3
32°	4507.8
33°	3983.2
34°	3453.2
35°	2980.7
37.5°	1905.0
40°	1102.2
42.5°	588.0
45°	273.1
47.5°	147.3
50°	47.6
52.5°	5.3
55°	0.0
57.5°	5.3



TEST NUMBER: P250427

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
60°	5.3
62.5°	0.0
65°	0.0
67.5°	5.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)