

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250343

Luminaire Tested: **LD8B200D010 ER8B200935 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250343
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B200935 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14438.0 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250343

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250343

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	711409
5°	700043
10°	621972
15°	513071
20°	432109
25°	364459
30°	272886
35°	154435
40°	61065
45°	16393
50°	3142
55°	0
60°	456
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250343

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2071.0	14.3
10°-20°	4501.3	31.2
20°-30°	4832.5	33.5
30°-40°	2611.8	18.1
40°-50°	407.5	2.8
50°-60°	11.2	0.1
60°-70°	2.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11404.8	79.0
0°-40°	14016.6	97.1
0°-60°	14435.3	100.0
0°-90°	14438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14438.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23070	
5°	22616	###
15°	16072	4501
25°	10712	4832
35°	4102	2612
45°	376	407
55°	0	11
65°	0	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250343

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBNOGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	23070.5
1°	23114.3
2°	23092.6
3°	23013.5
4°	22861.6
5°	22615.5
6°	22276.7
7°	21821.0
8°	21250.4
9°	20593.8
10°	19863.7
11°	19097.8
12°	18303.3
13°	17509.5
14°	16772.0
15°	16071.6
16°	15428.6
17°	14807.4
18°	14229.5
19°	13688.4
20°	13167.9
21°	12662.1
22°	12185.0
23°	11709.1
24°	11210.6
25°	10711.8
26°	10206.1
27°	9628.6
28°	8992.6
29°	8343.3
30°	7663.9
31°	6934.5
32°	6204.3
33°	5482.3
34°	4752.8
35°	4102.5
37.5°	2622.0
40°	1517.0
42.5°	809.2
45°	375.9
47.5°	202.7
50°	65.5
52.5°	7.4
55°	0.0
57.5°	7.4



TEST NUMBER: P250343

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	7.4
62.5°	0.0
65°	0.0
67.5°	7.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)