

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250028

Luminaire Tested: **LD8B200D010 ER8B2009727 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250028
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13951)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B2009727 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12865.0 lumens
Efficiency: N/A
Efficacy: 57.6 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250028

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P250028

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250028

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1700.7	13.2
10°-20°	3902.1	30.3
20°-30°	4145.5	32.2
30°-40°	2365.2	18.4
40°-50°	586.4	4.6
50°-60°	115.3	0.9
60°-70°	34.8	0.3
70°-80°	8.3	0.1
80°-90°	6.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9748.3	75.8
0°-40°	12113.5	94.2
0°-60°	12815.2	99.6
0°-90°	12865.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12865.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18738	
5°	18407	###
15°	14019	3902
25°	9152	4145
35°	3698	2365
45°	663	586
55°	107	115
65°	27	35
75°	0	8
85°	9	7
90°	0	



TEST NUMBER: P250028

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	18738.2
1°	18774.1
2°	18760.6
3°	18693.5
4°	18577.1
5°	18406.8
6°	18183.1
7°	17874.0
8°	17520.3
9°	17104.0
10°	16647.2
11°	16163.8
12°	15644.3
13°	15116.0
14°	14574.2
15°	14018.9
16°	13495.1
17°	12966.8
18°	12469.7
19°	11963.9
20°	11484.8
22.5°	10298.1
25°	9151.9
27.5°	7920.7
30°	6559.5
32.5°	5099.8
35°	3698.4
37.5°	2547.6
40°	1647.8
42.5°	1043.3
45°	662.6
47.5°	434.4
50°	273.1
52.5°	165.8
55°	107.4
57.5°	85.1
60°	53.7
62.5°	49.2
65°	26.9
67.5°	26.9
70°	22.5
72.5°	13.5
75°	0.0
77.5°	4.5
80°	4.5



TEST NUMBER: P250028

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
82.5°	9.0
85°	9.0
87.5°	4.5
90°	0.0

(END OF REPORT)