

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245368

Luminaire Tested: **LD8B40D010 ER8B40950 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245368  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B40D010 ER8B40950 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4532.0 lumens  
Efficiency: N/A  
Efficacy: 110.8 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245368

CATALOG NUMBER: LD8B40D010 ER8B40950 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P245368

CATALOG NUMBER: LD8B40D010 ER8B40950 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	79157
5°	79459
10°	80459
15°	82032
20°	83203
25°	83546
30°	80987
35°	73918
40°	63943
45°	50338
50°	32468
55°	15935
60°	6550
65°	2875
70°	829
75°	310
80°	231
85°	0



TEST NUMBER: P245368

CATALOG NUMBER: LD8B40D010 ER8B40950 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	245.1	5.4
10°-20°	726.2	16.0
20°-30°	1124.3	24.8
30°-40°	1218.0	26.9
40°-50°	876.5	19.3
50°-60°	293.2	6.5
60°-70°	44.3	1.0
70°-80°	3.8	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2095.6	46.2
0°-40°	3313.7	73.1
0°-60°	4483.3	98.9
0°-90°	4532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4532.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2567	
5°	2567	245
15°	2570	726
25°	2456	1124
35°	1964	1218
45°	1154	876
55°	296	293
65°	39	44
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P245368

CATALOG NUMBER: LD8B40D010 ER8B40950 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2567.0
2.5°	2567.0
5°	2567.0
7.5°	2568.3
10°	2569.6
12.5°	2572.2
15°	2569.6
17.5°	2559.1
20°	2535.5
22.5°	2500.1
25°	2455.5
27.5°	2384.7
30°	2274.5
32.5°	2130.2
35°	1963.6
37.5°	1783.9
40°	1588.5
42.5°	1378.6
45°	1154.3
47.5°	911.6
50°	676.8
52.5°	464.3
55°	296.4
57.5°	177.1
60°	106.2
62.5°	64.3
65°	39.4
67.5°	19.7
70°	9.2
72.5°	3.9
75°	2.6
77.5°	2.6
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)