

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245584

Luminaire Tested: **LD8B40D010 ER8B40950 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40950 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3634.0 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245584

CATALOG NUMBER: LD8B40D010 ER8B40950 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245584

CATALOG NUMBER: LD8B40D010 ER8B40950 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87254
5°	85192
10°	82523
15°	81330
20°	80371
25°	78643
30°	73663
35°	60148
40°	35907
45°	21569
50°	15543
55°	10580
60°	6636
65°	3254
70°	829
75°	310
80°	231
85°	0



TEST NUMBER: P245584

CATALOG NUMBER: LD8B40D010 ER8B40950 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.9	7.1
10°-20°	719.0	19.8
20°-30°	1055.8	29.1
30°-40°	957.1	26.3
40°-50°	409.7	11.3
50°-60°	181.3	5.0
60°-70°	48.4	1.3
70°-80°	3.8	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2033.6	56.0
0°-40°	2990.7	82.3
0°-60°	3581.7	98.6
0°-90°	3634.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3634.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2830	
5°	2752	259
15°	2548	719
25°	2311	1056
35°	1598	957
45°	495	410
55°	197	181
65°	45	48
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P245584

CATALOG NUMBER: LD8B40D010 ER8B40950 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2829.6
2.5°	2807.3
5°	2752.2
7.5°	2689.3
10°	2635.5
12.5°	2590.9
15°	2547.6
17.5°	2501.7
20°	2449.2
22.5°	2387.5
25°	2311.4
27.5°	2209.1
30°	2068.8
32.5°	1872.0
35°	1597.8
37.5°	1238.4
40°	892.0
42.5°	644.1
45°	494.6
47.5°	398.8
50°	324.0
52.5°	257.1
55°	196.8
57.5°	146.9
60°	107.6
62.5°	74.8
65°	44.6
67.5°	19.7
70°	9.2
72.5°	5.2
75°	2.6
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)