

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245745

Luminaire Tested: **LD8B30D010 ER8B30827 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30827 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2874.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245745

CATALOG NUMBER: LD8B30D010 ER8B30827 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245745

CATALOG NUMBER: LD8B30D010 ER8B30827 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50871
5°	50715
10°	50215
15°	49699
20°	49180
25°	48375
30°	47051
35°	44906
40°	41755
45°	35254
50°	23934
55°	12505
60°	5612
65°	2736
70°	1100
75°	667
80°	497
85°	318



TEST NUMBER: P245745

CATALOG NUMBER: LD8B30D010 ER8B30827 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.3	5.4
10°-20°	439.1	15.3
20°-30°	653.7	22.7
30°-40°	743.1	25.9
40°-50°	607.6	21.1
50°-60°	226.5	7.9
60°-70°	41.4	1.4
70°-80°	6.4	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1248.1	43.4
0°-40°	1991.2	69.3
0°-60°	2825.3	98.3
0°-90°	2874.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2874.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1650	
5°	1638	155
15°	1557	439
25°	1422	654
35°	1193	743
45°	808	608
55°	233	227
65°	38	41
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P245745

CATALOG NUMBER: LD8B30D010 ER8B30827 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1649.7
2.5°	1646.9
5°	1638.4
7.5°	1623.4
10°	1603.7
12.5°	1581.2
15°	1556.8
17.5°	1528.7
20°	1498.7
22.5°	1463.0
25°	1421.8
27.5°	1374.9
30°	1321.4
32.5°	1260.5
35°	1192.9
37.5°	1120.7
40°	1037.3
42.5°	934.1
45°	808.4
47.5°	657.4
50°	498.9
52.5°	351.7
55°	232.6
57.5°	146.3
60°	91.0
62.5°	58.1
65°	37.5
67.5°	21.6
70°	12.2
72.5°	7.5
75°	5.6
77.5°	3.8
80°	2.8
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)