

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244294

Luminaire Tested: **LD8B40D010 ER8B409727 8LBW0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244294
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B409727 8LBW0H
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3071.0 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244294

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P244294

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71		79	74	71		77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59		68	62	58		66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244294

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBW0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.0	6.3
10°-20°	556.8	18.1
20°-30°	837.9	27.3
30°-40°	829.5	27.0
40°-50°	421.5	13.7
50°-60°	169.8	5.5
60°-70°	51.4	1.7
70°-80°	8.8	0.3
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1588.7	51.7
0°-40°	2418.3	78.7
0°-60°	3009.6	98.0
0°-90°	3071.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3071.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2059	
5°	2047	194
15°	1974	557
25°	1830	838
35°	1365	830
45°	517	422
55°	183	170
65°	47	51
75°	7	9
85°	1	1
90°	0	



TEST NUMBER: P244294

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBW0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2059.2
1°	2054.8
2°	2051.2
3°	2050.4
4°	2049.5
5°	2046.8
6°	2043.3
7°	2036.2
8°	2025.5
9°	2015.7
10°	2005.1
11°	1996.2
12°	1990.0
13°	1985.6
14°	1980.2
15°	1974.0
16°	1966.0
17°	1956.3
18°	1944.7
19°	1931.4
20°	1916.3
21°	1900.3
22°	1884.4
23°	1867.5
24°	1849.8
25°	1830.2
26°	1808.9
27°	1781.4
28°	1749.5
29°	1711.3
30°	1666.9
32.5°	1537.3
35°	1365.1
37.5°	1150.3
40°	910.7
42.5°	687.9
45°	516.6
47.5°	395.0
50°	309.8
52.5°	240.5
55°	182.8
57.5°	135.8
60°	102.1
62.5°	72.8
65°	47.0



TEST NUMBER: P244294

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBW0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	29.3
70°	18.6
72.5°	11.5
75°	7.1
77.5°	4.4
80°	2.7
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)