

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245751

Luminaire Tested: **LD8B30D010 ER8B30830 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30830 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2946.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245751

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245751

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52144
5°	51987
10°	51474
15°	50944
20°	50411
25°	49587
30°	48229
35°	46031
40°	42798
45°	36139
50°	24533
55°	12817
60°	5754
65°	2809
70°	1127
75°	691
80°	515
85°	354



TEST NUMBER: P245751

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	5.4
10°-20°	450.1	15.3
20°-30°	670.1	22.7
30°-40°	761.7	25.9
40°-50°	622.8	21.1
50°-60°	232.2	7.9
60°-70°	42.5	1.4
70°-80°	6.6	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1279.3	43.4
0°-40°	2041.0	69.3
0°-60°	2896.0	98.3
0°-90°	2946.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2946.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1691	
5°	1680	159
15°	1596	450
25°	1457	670
35°	1223	762
45°	829	623
55°	238	232
65°	38	42
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P245751

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1691.0
2.5°	1688.1
5°	1679.5
7.5°	1664.1
10°	1643.9
12.5°	1620.8
15°	1595.8
17.5°	1567.0
20°	1536.2
22.5°	1499.7
25°	1457.4
27.5°	1409.3
30°	1354.5
32.5°	1292.0
35°	1222.8
37.5°	1148.8
40°	1063.2
42.5°	957.5
45°	828.7
47.5°	673.9
50°	511.4
52.5°	360.5
55°	238.4
57.5°	150.0
60°	93.3
62.5°	59.6
65°	38.5
67.5°	22.1
70°	12.5
72.5°	7.7
75°	5.8
77.5°	3.8
80°	2.9
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)