

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243953

Luminaire Tested: **LD8B50D010 ER8B50830 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50830 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5492.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243953

CATALOG NUMBER: LD8B50D010 ER8B50830 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243953

CATALOG NUMBER: LD8B50D010 ER8B50830 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295433
5°	282735
10°	251708
15°	202210
20°	158377
25°	127873
30°	99086
35°	56436
40°	21286
45°	9180
50°	3694
55°	1382
60°	740
65°	496
70°	307
75°	203
80°	0
85°	0



TEST NUMBER: P243953

CATALOG NUMBER: LD8B50D010 ER8B50830 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	838.4	15.3
10°-20°	1758.9	32.0
20°-30°	1721.2	31.3
30°-40°	952.2	17.3
40°-50°	184.3	3.4
50°-60°	28.3	0.5
60°-70°	6.9	0.1
70°-80°	1.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4318.4	78.6
0°-40°	5270.7	96.0
0°-60°	5483.2	99.8
0°-90°	5492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5492.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9581	
5°	9134	838
15°	6334	1759
25°	3758	1721
35°	1499	952
45°	210	184
55°	26	28
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P243953

CATALOG NUMBER: LD8B50D010 ER8B50830 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9580.7
2.5°	9448.9
5°	9134.0
7.5°	8692.5
10°	8038.7
12.5°	7212.1
15°	6334.1
17.5°	5510.9
20°	4826.3
22.5°	4259.8
25°	3758.3
27.5°	3286.0
30°	2782.8
32.5°	2192.4
35°	1499.2
37.5°	901.9
40°	528.8
42.5°	330.3
45°	210.5
47.5°	131.8
50°	77.0
52.5°	42.8
55°	25.7
57.5°	15.4
60°	12.0
62.5°	8.6
65°	6.8
67.5°	5.1
70°	3.4
72.5°	1.7
75°	1.7
77.5°	1.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)