

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245547

Luminaire Tested: **LD8B30D010 ER8B30840 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30840 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2752.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245547

CATALOG NUMBER: LD8B30D010 ER8B30840 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245547

CATALOG NUMBER: LD8B30D010 ER8B30840 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66076
5°	64515
10°	62493
15°	61591
20°	60866
25°	59556
30°	55785
35°	45549
40°	27192
45°	16332
50°	11773
55°	8010
60°	5026
65°	2466
70°	631
75°	238
80°	178
85°	0



TEST NUMBER: P245547

CATALOG NUMBER: LD8B30D010 ER8B30840 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.1	7.1
10°-20°	544.5	19.8
20°-30°	799.5	29.1
30°-40°	724.8	26.3
40°-50°	310.3	11.3
50°-60°	137.3	5.0
60°-70°	36.6	1.3
70°-80°	2.9	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1540.1	56.0
0°-40°	2264.9	82.3
0°-60°	2712.4	98.6
0°-90°	2752.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2752.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2143	
5°	2084	196
15°	1929	544
25°	1750	800
35°	1210	725
45°	374	310
55°	149	137
65°	34	37
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245547

CATALOG NUMBER: LD8B30D010 ER8B30840 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2142.8
2.5°	2126.0
5°	2084.2
7.5°	2036.6
10°	1995.8
12.5°	1962.0
15°	1929.3
17.5°	1894.5
20°	1854.8
22.5°	1808.1
25°	1750.4
27.5°	1673.0
30°	1566.7
32.5°	1417.6
35°	1210.0
37.5°	937.8
40°	675.5
42.5°	487.8
45°	374.5
47.5°	302.0
50°	245.4
52.5°	194.7
55°	149.0
57.5°	111.3
60°	81.5
62.5°	56.6
65°	33.8
67.5°	14.9
70°	7.0
72.5°	4.0
75°	2.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)