

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246555

Luminaire Tested: **LD8B30D010 ER8B30840 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30840 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3132.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246555

CATALOG NUMBER: LD8B30D010 ER8B30840 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246555

CATALOG NUMBER: LD8B30D010 ER8B30840 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54		63	58	53		62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45		55	49	45		54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63992
5°	62914
10°	60933
15°	59526
20°	58677
25°	57525
30°	54012
35°	44089
40°	27312
45°	18499
50°	16296
55°	15381
60°	15258
65°	14783
70°	13253
75°	11485
80°	9696
85°	7748



TEST NUMBER: P246555

CATALOG NUMBER: LD8B30D010 ER8B30840 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	6.1
10°-20°	526.6	16.8
20°-30°	772.3	24.7
30°-40°	705.9	22.5
40°-50°	349.5	11.2
50°-60°	258.4	8.3
60°-70°	198.6	6.3
70°-80°	103.6	3.3
80°-90°	25.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1490.1	47.6
0°-40°	2196.0	70.1
0°-60°	2804.0	89.5
0°-90°	3132.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3132.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2075	
5°	2032	191
15°	1865	527
25°	1691	772
35°	1171	706
45°	424	350
55°	286	258
65°	203	199
75°	96	104
85°	22	26
90°	0	



TEST NUMBER: P246555

CATALOG NUMBER: LD8B30D010 ER8B30840 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2075.2
2.5°	2064.2
5°	2032.5
7.5°	1989.7
10°	1946.0
12.5°	1903.3
15°	1864.6
17.5°	1827.8
20°	1788.1
22.5°	1743.4
25°	1690.7
27.5°	1618.2
30°	1516.9
32.5°	1374.8
35°	1171.2
37.5°	918.9
40°	678.5
42.5°	513.6
45°	424.2
47.5°	375.5
50°	339.7
52.5°	310.9
55°	286.1
57.5°	265.2
60°	247.4
62.5°	228.5
65°	202.6
67.5°	174.8
70°	147.0
72.5°	121.2
75°	96.4
77.5°	74.5
80°	54.6
82.5°	37.7
85°	21.9
87.5°	7.9
90°	0.0

(END OF REPORT)