

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244463

Luminaire Tested: **LD8B50D010 ER8B50835 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50835 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6035.0 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244463

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244463

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107998
5°	107640
10°	106821
15°	106068
20°	105350
25°	103964
30°	100753
35°	95063
40°	86393
45°	71087
50°	47383
55°	24682
60°	11631
65°	6100
70°	3047
75°	2121
80°	1580
85°	1274



TEST NUMBER: P244463

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.9	5.5
10°-20°	937.8	15.5
20°-30°	1402.8	23.2
30°-40°	1569.1	26.0
40°-50°	1230.9	20.4
50°-60°	449.1	7.4
60°-70°	91.6	1.5
70°-80°	19.7	0.3
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2670.4	44.2
0°-40°	4239.5	70.2
0°-60°	5919.6	98.1
0°-90°	6035.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6035.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3502	
5°	3477	330
15°	3322	938
25°	3056	1403
35°	2525	1569
45°	1630	1231
55°	459	449
65°	84	92
75°	18	20
85°	4	4
90°	0	



TEST NUMBER: P244463

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3502.3
2.5°	3496.9
5°	3477.4
7.5°	3448.9
10°	3411.5
12.5°	3368.8
15°	3322.5
17.5°	3270.9
20°	3210.4
22.5°	3139.2
25°	3055.6
27.5°	2952.4
30°	2829.6
32.5°	2685.4
35°	2525.3
37.5°	2345.5
40°	2146.2
42.5°	1909.5
45°	1630.1
47.5°	1315.1
50°	987.7
52.5°	692.3
55°	459.1
57.5°	293.6
60°	188.6
62.5°	124.6
65°	83.6
67.5°	53.4
70°	33.8
72.5°	23.1
75°	17.8
77.5°	12.5
80°	8.9
82.5°	5.3
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)