

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244895

Luminaire Tested: **LD8B50D010 ER8B50835 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244895  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B50D010 ER8B50835 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5918.0 lumens  
Efficiency: N/A  
Efficacy: 111.7 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244895

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244895

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	103468
5°	103148
10°	102221
15°	101209
20°	100120
25°	98541
30°	95835
35°	91468
40°	84767
45°	71571
50°	49100
55°	27085
60°	13611
65°	7661
70°	4174
75°	2967
80°	1900
85°	1274



TEST NUMBER: P244895

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	315.9	5.3
10°-20°	894.1	15.1
20°-30°	1331.1	22.5
30°-40°	1512.1	25.6
40°-50°	1236.0	20.9
50°-60°	484.3	8.2
60°-70°	112.9	1.9
70°-80°	27.2	0.5
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2541.1	42.9
0°-40°	4053.2	68.5
0°-60°	5773.6	97.6
0°-90°	5918.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5918.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3355	
5°	3332	316
15°	3170	894
25°	2896	1331
35°	2430	1512
45°	1641	1236
55°	504	484
65°	105	113
75°	25	27
85°	4	4
90°	0	



TEST NUMBER: P244895

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3355.4
2.5°	3350.1
5°	3332.3
7.5°	3302.0
10°	3264.6
12.5°	3218.4
15°	3170.3
17.5°	3113.3
20°	3051.0
22.5°	2978.0
25°	2896.2
27.5°	2800.0
30°	2691.5
32.5°	2568.6
35°	2429.8
37.5°	2276.7
40°	2105.8
42.5°	1899.3
45°	1641.2
47.5°	1338.6
50°	1023.5
52.5°	735.2
55°	503.8
57.5°	329.3
60°	220.7
62.5°	151.3
65°	105.0
67.5°	69.4
70°	46.3
72.5°	32.0
75°	24.9
77.5°	17.8
80°	10.7
82.5°	5.3
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)