

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243897

Luminaire Tested: **LD8B30D010 ER8B30850 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30850 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2987.0 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243897

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243897

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78	83	80	77	82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	451268
5°	313429
10°	164933
15°	104354
20°	77549
25°	60968
30°	43896
35°	18837
40°	6565
45°	2516
50°	585
55°	220
60°	0
65°	299
70°	90
75°	238
80°	355
85°	0



TEST NUMBER: P243897

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	811.8	27.2
10°-20°	943.2	31.6
20°-30°	814.0	27.3
30°-40°	353.2	11.8
40°-50°	55.4	1.9
50°-60°	4.0	0.1
60°-70°	2.1	0.1
70°-80°	2.3	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2569.0	86.0
0°-40°	2922.1	97.8
0°-60°	2981.5	99.8
0°-90°	2987.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2987.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14634	
5°	10126	812
15°	3269	943
25°	1792	814
35°	500	353
45°	58	55
55°	4	4
65°	4	2
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P243897

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	14634.3
2.5°	13215.1
5°	10125.6
7.5°	7221.4
10°	5267.4
12.5°	4041.7
15°	3268.8
17.5°	2749.2
20°	2363.2
22.5°	2034.0
25°	1791.9
27.5°	1536.7
30°	1232.8
32.5°	857.0
35°	500.4
37.5°	279.6
40°	163.1
42.5°	101.3
45°	57.7
47.5°	46.6
50°	12.2
52.5°	6.1
55°	4.1
57.5°	2.0
60°	0.0
62.5°	1.0
65°	4.1
67.5°	3.0
70°	1.0
72.5°	5.1
75°	2.0
77.5°	0.0
80°	2.0
82.5°	1.0
85°	0.0
87.5°	2.0
90°	0.0

(END OF REPORT)