

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246263

Luminaire Tested: **LD8B50D010 ER8B50835 8LBW0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246263  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B50D010 ER8B50835 8LBW0B  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3504.0 lumens  
Efficiency: N/A  
Efficacy: 66.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246263

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246263

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56	65	60	56	64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49	57	52	49	57	52	49	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	98806
5°	96320
10°	93758
15°	92012
20°	89619
25°	86442
30°	79314
35°	60814
40°	28935
45°	11016
50°	5378
55°	2199
60°	549
65°	131
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246263

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	293.4	8.4
10°-20°	811.1	23.1
20°-30°	1158.1	33.1
30°-40°	959.8	27.4
40°-50°	236.7	6.8
50°-60°	42.6	1.2
60°-70°	2.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2262.5	64.6
0°-40°	3222.4	92.0
0°-60°	3501.6	99.9
0°-90°	3504.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3504.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3204	
5°	3112	293
15°	2882	811
25°	2541	1158
35°	1616	960
45°	253	237
55°	41	43
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246263

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3204.2
2.5°	3177.6
5°	3111.7
7.5°	3047.7
10°	2994.3
12.5°	2942.7
15°	2882.2
17.5°	2811.1
20°	2731.0
22.5°	2640.3
25°	2540.6
27.5°	2405.4
30°	2227.5
32.5°	1976.6
35°	1615.5
37.5°	1167.1
40°	718.8
42.5°	418.1
45°	252.6
47.5°	167.2
50°	112.1
52.5°	72.9
55°	40.9
57.5°	19.6
60°	8.9
62.5°	3.6
65°	1.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)