

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244689

Luminaire Tested: **LD8B30D010 ER8B30850 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244689  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B30D010 ER8B30850 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3047.9 lumens  
Efficiency: N/A  
Efficacy: 112.5 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244689

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244689

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	68114
5°	66743
10°	64631
15°	63759
20°	63380
25°	62577
30°	59214
35°	48840
40°	30496
45°	19611
50°	15207
55°	11709
60°	8869
65°	5764
70°	2461
75°	1203
80°	533
85°	354



TEST NUMBER: P244689

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.8	6.7
10°-20°	564.2	18.5
20°-30°	840.4	27.6
30°-40°	780.5	25.6
40°-50°	368.6	12.1
50°-60°	198.1	6.5
60°-70°	79.5	2.6
70°-80°	12.5	0.4
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1607.5	52.7
0°-40°	2388.0	78.3
0°-60°	2954.7	96.9
0°-90°	3047.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3047.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2209	
5°	2156	203
15°	1997	564
25°	1839	840
35°	1297	781
45°	450	369
55°	218	198
65°	79	80
75°	10	12
85°	1	1
90°	0	



TEST NUMBER: P244689

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2208.9
2.5°	2193.7
5°	2156.2
7.5°	2108.6
10°	2064.1
12.5°	2027.6
15°	1997.2
17.5°	1965.8
20°	1931.4
22.5°	1891.9
25°	1839.2
27.5°	1765.3
30°	1663.0
32.5°	1513.1
35°	1297.4
37.5°	1021.9
40°	757.6
42.5°	564.1
45°	449.7
47.5°	375.7
50°	317.0
52.5°	264.3
55°	217.8
57.5°	177.2
60°	143.8
62.5°	112.4
65°	79.0
67.5°	46.6
70°	27.3
72.5°	16.2
75°	10.1
77.5°	6.1
80°	3.0
82.5°	2.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)