

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245261

Luminaire Tested: **LD8B50D010 ER8B50840 8LBM0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245261  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B50D010 ER8B50840 8LBM0WH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 4000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5552.0 lumens  
Efficiency: N/A  
Efficacy: 104.8 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245261

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBM0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P245261

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBM0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	214917
5°	219044
10°	208845
15°	184410
20°	159804
25°	135031
30°	101476
35°	67944
40°	38048
45°	15285
50°	5291
55°	1468
60°	833
65°	722
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245261

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBM0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	662.1	11.9
10°-20°	1611.2	29.0
20°-30°	1787.9	32.2
30°-40°	1132.7	20.4
40°-50°	314.3	5.7
50°-60°	36.0	0.6
60°-70°	7.1	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4061.2	73.1
0°-40°	5193.9	93.6
0°-60°	5544.2	99.9
0°-90°	5552.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5552.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6970	
5°	7076	662
15°	5776	1611
25°	3969	1788
35°	1805	1133
45°	350	314
55°	27	36
65°	10	7
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245261

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBM0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6969.6
2.5°	7021.2
5°	7076.4
7.5°	6966.1
10°	6669.8
12.5°	6247.2
15°	5776.5
17.5°	5314.2
20°	4869.8
22.5°	4433.8
25°	3968.7
27.5°	3424.8
30°	2849.9
32.5°	2293.0
35°	1804.9
37.5°	1363.9
40°	945.2
42.5°	587.8
45°	350.5
47.5°	201.6
50°	110.3
52.5°	54.0
55°	27.3
57.5°	20.5
60°	13.5
62.5°	7.1
65°	9.9
67.5°	5.0
70°	0.0
72.5°	1.4
75°	0.0
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245261

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBM0WH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)