

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244509

Luminaire Tested: **LD8B30D010 ER8B30927 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30927 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2656.1 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244509

CATALOG NUMBER: LD8B30D010 ER8B30927 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244509

CATALOG NUMBER: LD8B30D010 ER8B30927 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244509

CATALOG NUMBER: LD8B30D010 ER8B30927 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.2	5.5
10°-20°	412.7	15.5
20°-30°	617.4	23.2
30°-40°	690.6	26.0
40°-50°	541.8	20.4
50°-60°	197.7	7.4
60°-70°	40.3	1.5
70°-80°	8.7	0.3
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1175.3	44.2
0°-40°	1865.9	70.2
0°-60°	2605.3	98.1
0°-90°	2656.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2656.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1542	
5°	1530	145
15°	1462	413
25°	1345	617
35°	1111	691
45°	717	542
55°	202	198
65°	37	40
75°	8	9
85°	2	2
90°	0	



TEST NUMBER: P244509

CATALOG NUMBER: LD8B30D010 ER8B30927 8LBS0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1541.5
2.5°	1539.1
5°	1530.4
7.5°	1518.0
10°	1501.4
12.5°	1482.6
15°	1462.3
17.5°	1439.6
20°	1413.0
22.5°	1381.6
25°	1344.8
27.5°	1299.4
30°	1245.4
32.5°	1181.9
35°	1111.4
37.5°	1032.3
40°	944.6
42.5°	840.4
45°	717.4
47.5°	578.8
50°	434.7
52.5°	304.7
55°	202.0
57.5°	129.3
60°	83.0
62.5°	54.8
65°	36.8
67.5°	23.5
70°	14.8
72.5°	10.2
75°	7.9
77.5°	5.5
80°	3.9
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)