

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244803

Luminaire Tested: **LD8B30D010 ER8B30930 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30930 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2245.4 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244803

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244803

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	59		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244803

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.6	13.2
10°-20°	681.8	30.4
20°-30°	723.4	32.2
30°-40°	412.7	18.4
40°-50°	102.3	4.6
50°-60°	20.1	0.9
60°-70°	6.0	0.3
70°-80°	1.3	0.1
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1701.8	75.8
0°-40°	2114.5	94.2
0°-60°	2236.9	99.6
0°-90°	2245.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2245.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3270	
5°	3212	297
15°	2447	682
25°	1597	723
35°	645	413
45°	116	102
55°	19	20
65°	4	6
75°	0	1
85°	2	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244803

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3270.0
2.5°	3268.5
5°	3212.1
7.5°	3088.4
10°	2905.4
12.5°	2684.6
15°	2446.7
17.5°	2220.0
20°	2004.3
22.5°	1797.0
25°	1596.9
27.5°	1381.9
30°	1144.8
32.5°	889.8
35°	645.4
37.5°	444.6
40°	287.4
42.5°	182.3
45°	115.6
47.5°	75.7
50°	47.4
52.5°	28.8
55°	18.6
57.5°	14.9
60°	9.6
62.5°	8.9
65°	4.5
67.5°	4.5
70°	3.7
72.5°	2.1
75°	0.0
77.5°	0.7
80°	0.7
82.5°	1.6
85°	1.6
87.5°	0.7
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244803

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)