

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244947

Luminaire Tested: **LD8B30D010 ER8B30930 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244947  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B30D010 ER8B30930 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2745.3 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244947

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244947

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244947

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.5	5.3
10°-20°	414.8	15.1
20°-30°	617.5	22.5
30°-40°	701.5	25.6
40°-50°	573.4	20.9
50°-60°	224.7	8.2
60°-70°	52.4	1.9
70°-80°	12.6	0.5
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.8	42.9
0°-40°	1880.3	68.5
0°-60°	2678.3	97.6
0°-90°	2745.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2745.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1556	
5°	1546	147
15°	1471	415
25°	1344	618
35°	1127	701
45°	761	573
55°	234	225
65°	49	52
75°	12	13
85°	2	2
90°	0	



TEST NUMBER: P244947

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1556.5
2.5°	1554.0
5°	1545.9
7.5°	1531.7
10°	1514.5
12.5°	1492.9
15°	1470.6
17.5°	1444.3
20°	1415.4
22.5°	1381.5
25°	1343.5
27.5°	1298.9
30°	1248.6
32.5°	1191.6
35°	1127.2
37.5°	1056.1
40°	976.8
42.5°	881.1
45°	761.4
47.5°	620.9
50°	474.9
52.5°	341.0
55°	233.7
57.5°	152.8
60°	102.3
62.5°	70.2
65°	48.8
67.5°	32.2
70°	21.5
72.5°	14.9
75°	11.5
77.5°	8.3
80°	4.9
82.5°	2.5
85°	1.7
87.5°	0.8
90°	0.0

(END OF REPORT)