

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246315

Luminaire Tested: **LD8B30D010 ER8B30930 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30930 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1625.4 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246315

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246315

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93						
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86						
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80						
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	74						
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68						
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	65	63						
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58						
8	77	67	61	57	76	67	61	57	66	60	56	65	60	56	64	59	56	54						
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51						
10	70	59	53	49	68	59	53	49	58	53	49	57	52	49	57	52	49	47						

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246315

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.1	8.4
10°-20°	376.2	23.1
20°-30°	537.2	33.1
30°-40°	445.2	27.4
40°-50°	109.8	6.8
50°-60°	19.8	1.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.5	64.6
0°-40°	1494.8	92.0
0°-60°	1624.3	99.9
0°-90°	1625.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1625.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1486	
5°	1444	136
15°	1337	376
25°	1178	537
35°	749	445
45°	117	110
55°	19	20
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246315

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1486.4
2.5°	1474.0
5°	1443.5
7.5°	1413.8
10°	1389.0
12.5°	1365.0
15°	1337.0
17.5°	1304.1
20°	1266.8
22.5°	1224.8
25°	1178.5
27.5°	1115.8
30°	1033.3
32.5°	917.0
35°	749.4
37.5°	541.4
40°	333.4
42.5°	193.9
45°	117.1
47.5°	77.6
50°	52.0
52.5°	33.9
55°	18.9
57.5°	9.1
60°	4.1
62.5°	1.7
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)