

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246579

Luminaire Tested: **LD8B30D010 ER8B30935 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30935 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2689.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246579

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246579

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54941
5°	54015
10°	52316
15°	51104
20°	50378
25°	49389
30°	46371
35°	37851
40°	23448
45°	15882
50°	13994
55°	13204
60°	13099
65°	12696
70°	11378
75°	9853
80°	8328
85°	6652



TEST NUMBER: P246579

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	6.1
10°-20°	452.1	16.8
20°-30°	663.1	24.7
30°-40°	606.1	22.5
40°-50°	300.1	11.2
50°-60°	221.9	8.3
60°-70°	170.6	6.3
70°-80°	88.9	3.3
80°-90°	22.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1279.3	47.6
0°-40°	1885.4	70.1
0°-60°	2407.4	89.5
0°-90°	2689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1782	
5°	1745	164
15°	1601	452
25°	1452	663
35°	1006	606
45°	364	300
55°	246	222
65°	174	171
75°	83	89
85°	19	22
90°	0	



TEST NUMBER: P246579

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1781.7
2.5°	1772.3
5°	1745.0
7.5°	1708.3
10°	1670.8
12.5°	1634.1
15°	1600.8
17.5°	1569.3
20°	1535.2
22.5°	1496.8
25°	1451.6
27.5°	1389.3
30°	1302.3
32.5°	1180.4
35°	1005.5
37.5°	788.9
40°	582.5
42.5°	440.9
45°	364.2
47.5°	322.4
50°	291.7
52.5°	266.9
55°	245.6
57.5°	227.7
60°	212.4
62.5°	196.2
65°	174.0
67.5°	150.1
70°	126.2
72.5°	104.1
75°	82.7
77.5°	64.0
80°	46.9
82.5°	32.4
85°	18.8
87.5°	6.8
90°	0.0

(END OF REPORT)