

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244799

Luminaire Tested: **LD8B50D010 ER8B50927 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244799
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50927 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3790.2 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244799

CATALOG NUMBER: LD8B50D010 ER8B50927 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244799

CATALOG NUMBER: LD8B50D010 ER8B50927 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	59		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244799

CATALOG NUMBER: LD8B50D010 ER8B50927 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	500.7	13.2
10°-20°	1150.8	30.4
20°-30°	1221.0	32.2
30°-40°	696.7	18.4
40°-50°	172.7	4.6
50°-60°	33.9	0.9
60°-70°	10.2	0.3
70°-80°	2.3	0.1
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2872.5	75.8
0°-40°	3569.2	94.2
0°-60°	3775.8	99.6
0°-90°	3790.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3790.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5520	
5°	5422	501
15°	4130	1151
25°	2695	1221
35°	1089	697
45°	195	173
55°	31	34
65°	8	10
75°	0	2
85°	3	2
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244799

CATALOG NUMBER: LD8B50D010 ER8B50927 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5519.7
2.5°	5517.1
5°	5422.0
7.5°	5213.1
10°	4904.3
12.5°	4531.5
15°	4130.0
17.5°	3747.3
20°	3383.3
22.5°	3033.2
25°	2695.4
27.5°	2332.6
30°	1932.4
32.5°	1502.1
35°	1089.4
37.5°	750.5
40°	485.2
42.5°	307.7
45°	195.2
47.5°	127.7
50°	80.1
52.5°	48.7
55°	31.4
57.5°	25.1
60°	16.2
62.5°	15.0
65°	7.5
67.5°	7.5
70°	6.3
72.5°	3.7
75°	0.0
77.5°	1.2
80°	1.2
82.5°	2.6
85°	2.6
87.5°	1.2
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244799

CATALOG NUMBER: LD8B50D010 ER8B50927 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)