

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245793

Luminaire Tested: **LD8B30D010 ER8B30940 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30940 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2729.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245793

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245793

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48302
5°	48158
10°	47682
15°	47193
20°	46699
25°	45933
30°	44679
35°	42643
40°	39646
45°	33474
50°	22730
55°	11876
60°	5329
65°	2598
70°	1046
75°	631
80°	479
85°	318



TEST NUMBER: P245793

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.4	5.4
10°-20°	417.0	15.3
20°-30°	620.7	22.7
30°-40°	705.6	25.9
40°-50°	577.0	21.1
50°-60°	215.1	7.9
60°-70°	39.3	1.4
70°-80°	6.1	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1185.1	43.4
0°-40°	1890.7	69.3
0°-60°	2682.8	98.3
0°-90°	2729.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2729.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1566	
5°	1556	147
15°	1478	417
25°	1350	621
35°	1133	706
45°	768	577
55°	221	215
65°	36	39
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P245793

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1566.4
2.5°	1563.8
5°	1555.8
7.5°	1541.5
10°	1522.8
12.5°	1501.4
15°	1478.3
17.5°	1451.6
20°	1423.1
22.5°	1389.2
25°	1350.0
27.5°	1305.5
30°	1254.8
32.5°	1196.9
35°	1132.8
37.5°	1064.2
40°	984.9
42.5°	887.0
45°	767.6
47.5°	624.3
50°	473.8
52.5°	333.9
55°	220.9
57.5°	138.9
60°	86.4
62.5°	55.2
65°	35.6
67.5°	20.5
70°	11.6
72.5°	7.1
75°	5.3
77.5°	3.6
80°	2.7
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)