

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244949

Luminaire Tested: **LD8B50D010 ER8B50930 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244949  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B50D010 ER8B50930 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4886.5 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244949

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244949

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244949

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	260.8	5.3
10°-20°	738.2	15.1
20°-30°	1099.1	22.5
30°-40°	1248.5	25.6
40°-50°	1020.6	20.9
50°-60°	399.9	8.2
60°-70°	93.2	1.9
70°-80°	22.5	0.5
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2098.2	42.9
0°-40°	3346.7	68.5
0°-60°	4767.2	97.6
0°-90°	4886.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4886.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2771	
5°	2751	261
15°	2618	738
25°	2391	1099
35°	2006	1249
45°	1355	1021
55°	416	400
65°	87	93
75°	21	22
85°	3	4
90°	0	



TEST NUMBER: P244949

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2770.6
2.5°	2766.2
5°	2751.4
7.5°	2726.5
10°	2695.6
12.5°	2657.3
15°	2617.6
17.5°	2570.7
20°	2519.2
22.5°	2458.9
25°	2391.3
27.5°	2312.0
30°	2222.3
32.5°	2120.9
35°	2006.3
37.5°	1879.8
40°	1738.8
42.5°	1568.3
45°	1355.2
47.5°	1105.3
50°	845.1
52.5°	607.0
55°	416.0
57.5°	272.0
60°	182.3
62.5°	124.9
65°	86.8
67.5°	57.3
70°	38.2
72.5°	26.5
75°	20.6
77.5°	14.7
80°	8.9
82.5°	4.4
85°	2.9
87.5°	1.5
90°	0.0

(END OF REPORT)