

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245583

Luminaire Tested: **LD8B30D010 ER8B30950 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30950 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2554.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245583

CATALOG NUMBER: LD8B30D010 ER8B30950 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245583

CATALOG NUMBER: LD8B30D010 ER8B30950 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61324
5°	59875
10°	57996
15°	57160
20°	56485
25°	55272
30°	51769
35°	42274
40°	25235
45°	15159
50°	10923
55°	7435
60°	4662
65°	2284
70°	586
75°	214
80°	160
85°	0



TEST NUMBER: P245583

CATALOG NUMBER: LD8B30D010 ER8B30950 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	7.1
10°-20°	505.3	19.8
20°-30°	742.0	29.1
30°-40°	672.6	26.3
40°-50°	287.9	11.3
50°-60°	127.4	5.0
60°-70°	34.0	1.3
70°-80°	2.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1429.3	56.0
0°-40°	2101.9	82.3
0°-60°	2517.3	98.6
0°-90°	2554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1989	
5°	1934	182
15°	1790	505
25°	1624	742
35°	1123	673
45°	348	288
55°	138	127
65°	31	34
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245583

CATALOG NUMBER: LD8B30D010 ER8B30950 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1988.7
2.5°	1973.0
5°	1934.3
7.5°	1890.0
10°	1852.2
12.5°	1820.9
15°	1790.5
17.5°	1758.2
20°	1721.3
22.5°	1678.0
25°	1624.5
27.5°	1552.6
30°	1453.9
32.5°	1315.6
35°	1123.0
37.5°	870.3
40°	626.9
42.5°	452.7
45°	347.6
47.5°	280.3
50°	227.7
52.5°	180.7
55°	138.3
57.5°	103.3
60°	75.6
62.5°	52.6
65°	31.3
67.5°	13.8
70°	6.5
72.5°	3.7
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)