

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244719

Luminaire Tested: **LD8B30D010 ER8B30950 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30950 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2775.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244719

CATALOG NUMBER: LD8B30D010 ER8B30950 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244719

CATALOG NUMBER: LD8B30D010 ER8B30950 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62015
5°	60766
10°	58842
15°	58048
20°	57702
25°	56973
30°	53912
35°	44465
40°	27763
45°	17854
50°	13845
55°	10656
60°	8073
65°	5246
70°	2245
75°	1096
80°	497
85°	318



TEST NUMBER: P244719

CATALOG NUMBER: LD8B30D010 ER8B30950 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	6.7
10°-20°	513.7	18.5
20°-30°	765.2	27.6
30°-40°	710.6	25.6
40°-50°	335.6	12.1
50°-60°	180.3	6.5
60°-70°	72.4	2.6
70°-80°	11.4	0.4
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1463.5	52.7
0°-40°	2174.1	78.3
0°-60°	2690.1	96.9
0°-90°	2775.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2775.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2011	
5°	1963	185
15°	1818	514
25°	1674	765
35°	1181	711
45°	409	336
55°	198	180
65°	72	72
75°	9	11
85°	1	1
90°	0	



TEST NUMBER: P244719

CATALOG NUMBER: LD8B30D010 ER8B30950 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2011.1
2.5°	1997.2
5°	1963.1
7.5°	1919.8
10°	1879.2
12.5°	1846.0
15°	1818.3
17.5°	1789.8
20°	1758.4
22.5°	1722.4
25°	1674.5
27.5°	1607.2
30°	1514.1
32.5°	1377.6
35°	1181.2
37.5°	930.4
40°	689.7
42.5°	513.6
45°	409.4
47.5°	342.1
50°	288.6
52.5°	240.7
55°	198.2
57.5°	161.4
60°	130.9
62.5°	102.4
65°	71.9
67.5°	42.4
70°	24.9
72.5°	14.8
75°	9.2
77.5°	5.5
80°	2.8
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)