

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243867

Luminaire Tested: **LD8B30D010 ER8B309730 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B309730 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2404.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0LI

Luminous Intensity Polar Plot






TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.7	5.8
10°-20°	459.5	19.1
20°-30°	723.1	30.1
30°-40°	687.8	28.6
40°-50°	317.1	13.2
50°-60°	72.0	3.0
60°-70°	4.7	0.2
70°-80°	1.0	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1321.3	55.0
0°-40°	2009.1	83.6
0°-60°	2398.2	99.8
0°-90°	2404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2404.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1383	
5°	1419	139
15°	1630	460
25°	1586	723
35°	1127	688
45°	388	317
55°	70	72
65°	3	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1383.2
1°	1382.5
2°	1385.2
3°	1393.1
4°	1404.9
5°	1418.7
6°	1435.8
7°	1454.2
8°	1473.3
9°	1495.7
10°	1519.3
11°	1543.0
12°	1568.0
13°	1591.7
14°	1613.4
15°	1630.5
16°	1643.0
17°	1651.5
18°	1655.5
19°	1654.8
20°	1650.2
21°	1642.3
22°	1632.5
23°	1619.3
24°	1604.2
25°	1585.8
26°	1564.1
27°	1536.4
28°	1503.5
29°	1465.4
30°	1421.3
32.5°	1289.1
35°	1127.3
37.5°	939.2
40°	734.0
42.5°	542.6
45°	388.1
47.5°	274.9
50°	189.4
52.5°	121.0
55°	69.7
57.5°	34.9
60°	15.1
62.5°	5.9
65°	3.3



TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2.0
70°	1.3
72.5°	1.3
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)