

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244882

Luminaire Tested: **LD8B40D010 ER8B40827 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244882  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B40D010 ER8B40827 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 2700 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4436.9 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244882

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244882

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	77575
5°	77336
10°	76639
15°	75880
20°	75065
25°	73880
30°	71851
35°	68576
40°	63553
45°	53661
50°	36814
55°	20306
60°	10207
65°	5742
70°	3129
75°	2228
80°	1421
85°	955



TEST NUMBER: P244882

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	236.8	5.3
10°-20°	670.3	15.1
20°-30°	998.0	22.5
30°-40°	1133.7	25.6
40°-50°	926.7	20.9
50°-60°	363.1	8.2
60°-70°	84.6	1.9
70°-80°	20.4	0.5
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1905.2	42.9
0°-40°	3038.9	68.5
0°-60°	4328.7	97.6
0°-90°	4436.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4436.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2516	
5°	2498	237
15°	2377	670
25°	2171	998
35°	1822	1134
45°	1230	927
55°	378	363
65°	79	85
75°	19	20
85°	3	3
90°	0	



TEST NUMBER: P244882

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2515.7
2.5°	2511.7
5°	2498.4
7.5°	2475.7
10°	2447.6
12.5°	2412.9
15°	2376.9
17.5°	2334.2
20°	2287.5
22.5°	2232.8
25°	2171.4
27.5°	2099.3
30°	2017.9
32.5°	1925.8
35°	1821.7
37.5°	1706.9
40°	1578.8
42.5°	1424.0
45°	1230.5
47.5°	1003.6
50°	767.4
52.5°	551.2
55°	377.7
57.5°	246.9
60°	165.5
62.5°	113.4
65°	78.7
67.5°	52.0
70°	34.7
72.5°	24.0
75°	18.7
77.5°	13.3
80°	8.0
82.5°	4.0
85°	2.7
87.5°	1.3
90°	0.0

(END OF REPORT)