

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246250

Luminaire Tested: **LD8B40D010 ER8B40827 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40827 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2628.0 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246250

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246250

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | | 101 | 99 | 98 | | 97 | 96 | 95 | 93 |
| 2 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 97 | 94 | 92 | | 94 | 92 | 90 | | 92 | 90 | 88 | 86 |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 85 | 91 | 87 | 84 | | 89 | 85 | 82 | | 86 | 84 | 81 | 80 |
| 4 | 96 | 88 | 83 | 78 | 94 | 87 | 82 | 78 | 85 | 80 | 77 | | 83 | 79 | 76 | | 81 | 78 | 75 | 74 |
| 5 | 91 | 82 | 76 | 72 | 89 | 81 | 76 | 71 | 80 | 75 | 71 | | 78 | 74 | 70 | | 76 | 73 | 70 | 68 |
| 6 | 86 | 77 | 71 | 66 | 85 | 76 | 70 | 66 | 74 | 69 | 65 | | 73 | 68 | 65 | | 72 | 68 | 65 | 63 |
| 7 | 82 | 72 | 66 | 61 | 80 | 71 | 65 | 61 | 70 | 64 | 61 | | 69 | 64 | 60 | | 67 | 63 | 60 | 58 |
| 8 | 77 | 67 | 61 | 57 | 76 | 67 | 61 | 57 | 66 | 60 | 56 | | 65 | 60 | 56 | | 64 | 59 | 56 | 54 |
| 9 | 73 | 63 | 57 | 53 | 72 | 63 | 57 | 53 | 62 | 56 | 52 | | 61 | 56 | 52 | | 60 | 55 | 52 | 51 |
| 10 | 70 | 59 | 53 | 49 | 68 | 59 | 53 | 49 | 58 | 53 | 49 | | 57 | 52 | 49 | | 57 | 52 | 49 | 47 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 74106 |
| 5° | 72241 |
| 10° | 70317 |
| 15° | 69010 |
| 20° | 67212 |
| 25° | 64833 |
| 30° | 59485 |
| 35° | 45610 |
| 40° | 21701 |
| 45° | 8264 |
| 50° | 4035 |
| 55° | 1650 |
| 60° | 413 |
| 65° | 95 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P246250

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBW0B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 220.0 | 8.4 |
| 10°-20° | 608.3 | 23.1 |
| 20°-30° | 868.6 | 33.1 |
| 30°-40° | 719.9 | 27.4 |
| 40°-50° | 177.5 | 6.8 |
| 50°-60° | 32.0 | 1.2 |
| 60°-70° | 1.8 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1696.9 | 64.6 |
| 0°-40° | 2416.8 | 92.0 |
| 0°-60° | 2626.2 | 99.9 |
| 0°-90° | 2628.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2628.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2403 | |
| 5° | 2334 | 220 |
| 15° | 2162 | 608 |
| 25° | 1906 | 869 |
| 35° | 1212 | 720 |
| 45° | 190 | 178 |
| 55° | 31 | 32 |
| 65° | 1 | 2 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P246250

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBW0B

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2403.2 |
| 2.5° | 2383.2 |
| 5° | 2333.8 |
| 7.5° | 2285.8 |
| 10° | 2245.7 |
| 12.5° | 2207.0 |
| 15° | 2161.7 |
| 17.5° | 2108.3 |
| 20° | 2048.2 |
| 22.5° | 1980.2 |
| 25° | 1905.5 |
| 27.5° | 1804.1 |
| 30° | 1670.6 |
| 32.5° | 1482.5 |
| 35° | 1211.6 |
| 37.5° | 875.3 |
| 40° | 539.1 |
| 42.5° | 313.6 |
| 45° | 189.5 |
| 47.5° | 125.4 |
| 50° | 84.1 |
| 52.5° | 54.7 |
| 55° | 30.7 |
| 57.5° | 14.7 |
| 60° | 6.7 |
| 62.5° | 2.7 |
| 65° | 1.3 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)