

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243929

Luminaire Tested: **LD8B50D010 ER8B50950 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50950 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4840.0 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243929

CATALOG NUMBER: LD8B50D010 ER8B50950 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243929

CATALOG NUMBER: LD8B50D010 ER8B50950 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78	83	80	77	82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	731215
5°	507867
10°	267251
15°	169092
20°	125660
25°	98792
30°	71124
35°	30522
40°	10639
45°	4082
50°	945
55°	355
60°	0
65°	482
70°	144
75°	393
80°	586
85°	0



TEST NUMBER: P243929

CATALOG NUMBER: LD8B50D010 ER8B50950 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1315.4	27.2
10°-20°	1528.3	31.6
20°-30°	1319.0	27.3
30°-40°	572.2	11.8
40°-50°	89.7	1.9
50°-60°	6.5	0.1
60°-70°	3.5	0.1
70°-80°	3.7	0.1
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4162.7	86.0
0°-40°	4734.9	97.8
0°-60°	4831.1	99.8
0°-90°	4840.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4840.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23713	
5°	16407	###
15°	5297	1528
25°	2904	1319
35°	811	572
45°	94	90
55°	7	6
65°	7	3
75°	3	4
85°	0	2
90°	0	



TEST NUMBER: P243929

CATALOG NUMBER: LD8B50D010 ER8B50950 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	23712.8
2.5°	21413.2
5°	16407.1
7.5°	11701.3
10°	8535.1
12.5°	6549.0
15°	5296.7
17.5°	4454.7
20°	3829.3
22.5°	3295.9
25°	2903.6
27.5°	2489.9
30°	1997.5
32.5°	1388.6
35°	810.8
37.5°	453.0
40°	264.3
42.5°	164.1
45°	93.6
47.5°	75.5
50°	19.7
52.5°	9.8
55°	6.6
57.5°	3.3
60°	0.0
62.5°	1.6
65°	6.6
67.5°	4.9
70°	1.6
72.5°	8.2
75°	3.3
77.5°	0.0
80°	3.3
82.5°	1.6
85°	0.0
87.5°	3.3
90°	0.0

(END OF REPORT)