

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244666

Luminaire Tested: **LD8B40D010 ER8B40827 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40827 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4015.0 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244666

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244666

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89724
5°	87919
10°	85134
15°	83989
20°	83485
25°	82430
30°	78000
35°	64334
40°	40169
45°	25830
50°	20033
55°	15419
60°	11681
65°	7596
70°	3246
75°	1585
80°	710
85°	460



TEST NUMBER: P244666

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.1	6.7
10°-20°	743.3	18.5
20°-30°	1107.1	27.6
30°-40°	1028.1	25.6
40°-50°	485.6	12.1
50°-60°	260.9	6.5
60°-70°	104.8	2.6
70°-80°	16.4	0.4
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2117.5	52.7
0°-40°	3145.6	78.3
0°-60°	3892.1	96.9
0°-90°	4015.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4015.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2910	
5°	2840	267
15°	2631	743
25°	2423	1107
35°	1709	1028
45°	592	486
55°	287	261
65°	104	105
75°	13	16
85°	1	2
90°	0	



TEST NUMBER: P244666

CATALOG NUMBER: LD8B40D010 ER8B40827 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2909.7
2.5°	2889.7
5°	2840.3
7.5°	2777.6
10°	2718.9
12.5°	2670.9
15°	2630.9
17.5°	2589.5
20°	2544.1
22.5°	2492.1
25°	2422.7
27.5°	2325.4
30°	2190.6
32.5°	1993.2
35°	1709.0
37.5°	1346.1
40°	997.9
42.5°	743.1
45°	592.3
47.5°	495.0
50°	417.6
52.5°	348.2
55°	286.8
57.5°	233.5
60°	189.4
62.5°	148.1
65°	104.1
67.5°	61.4
70°	36.0
72.5°	21.3
75°	13.3
77.5°	8.0
80°	4.0
82.5°	2.7
85°	1.3
87.5°	0.0
90°	0.0

(END OF REPORT)