

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246472

Luminaire Tested: **LD8B40D010 ER8B40830 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40830 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3856.0 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246472

CATALOG NUMBER: LD8B40D010 ER8B40830 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P246472

CATALOG NUMBER: LD8B40D010 ER8B40830 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56	65	60	55	64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68882
5°	68805
10°	68445
15°	67947
20°	67196
25°	66136
30°	64195
35°	61176
40°	56661
45°	47543
50°	31432
55°	15516
60°	6161
65°	2393
70°	370
75°	0
80°	0
85°	0



TEST NUMBER: P246472

CATALOG NUMBER: LD8B40D010 ER8B40830 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.0	5.5
10°-20°	599.9	15.6
20°-30°	893.0	23.2
30°-40°	1011.4	26.2
40°-50°	817.7	21.2
50°-60°	283.6	7.4
60°-70°	38.8	1.0
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1703.9	44.2
0°-40°	2715.4	70.4
0°-60°	3816.7	99.0
0°-90°	3856.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3856.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2234	
5°	2223	211
15°	2128	600
25°	1944	893
35°	1625	1011
45°	1090	818
55°	289	284
65°	33	39
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P246472

CATALOG NUMBER: LD8B40D010 ER8B40830 8LBS0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2233.8
2.5°	2231.0
5°	2222.8
7.5°	2206.4
10°	2185.9
12.5°	2158.5
15°	2128.4
17.5°	2090.1
20°	2047.7
22.5°	1998.5
25°	1943.8
27.5°	1878.1
30°	1802.9
32.5°	1718.1
35°	1625.1
37.5°	1522.5
40°	1407.6
42.5°	1266.7
45°	1090.2
47.5°	876.8
50°	655.2
52.5°	448.7
55°	288.6
57.5°	171.0
60°	99.9
62.5°	58.8
65°	32.8
67.5°	15.0
70°	4.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)