

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245686

Luminaire Tested: **LD8B40D010 ER8B40835 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245686  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B40D010 ER8B40835 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3874.1 lumens  
Efficiency: N/A  
Efficacy: 94.7 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245686

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245686

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	151530
5°	147685
10°	132425
15°	117915
20°	107592
25°	97707
30°	80129
35°	52762
40°	26294
45°	9777
50°	2974
55°	333
60°	204
65°	0
70°	144
75°	584
80°	0
85°	566



TEST NUMBER: P245686

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	437.5	11.3
10°-20°	1040.1	26.8
20°-30°	1295.6	33.4
30°-40°	874.3	22.6
40°-50°	206.6	5.3
50°-60°	15.0	0.4
60°-70°	2.6	0.1
70°-80°	1.9	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2773.2	71.6
0°-40°	3647.5	94.2
0°-60°	3869.1	99.9
0°-90°	3874.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3874.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4914	
5°	4771	437
15°	3694	1040
25°	2872	1296
35°	1402	874
45°	224	207
55°	6	15
65°	0	3
75°	5	2
85°	2	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245686

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4914.0
2.5°	4906.2
5°	4771.1
7.5°	4527.9
10°	4229.2
12.5°	3944.7
15°	3693.6
17.5°	3477.2
20°	3278.7
22.5°	3086.4
25°	2871.7
27.5°	2592.1
30°	2250.4
32.5°	1837.2
35°	1401.6
37.5°	1003.0
40°	653.2
42.5°	390.9
45°	224.2
47.5°	125.6
50°	62.0
52.5°	28.6
55°	6.2
57.5°	1.6
60°	3.3
62.5°	4.9
65°	0.0
67.5°	3.3
70°	1.6
72.5°	1.6
75°	4.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.6
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245686

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBM0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)