

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244367

Luminaire Tested: **LD8B50D010 ER8B509727 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B509727 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3472.0 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244367

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244367

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244367

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	445.7	12.8
10°-20°	996.0	28.7
20°-30°	1132.4	32.6
30°-40°	665.1	19.2
40°-50°	178.5	5.1
50°-60°	42.3	1.2
60°-70°	9.7	0.3
70°-80°	2.1	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2574.1	74.1
0°-40°	3239.2	93.3
0°-60°	3460.0	99.7
0°-90°	3472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3472.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5300	
5°	4925	446
15°	3562	996
25°	2499	1132
35°	1035	665
45°	213	178
55°	42	42
65°	9	10
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P244367

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5300.0
1°	5270.7
2°	5216.8
3°	5140.6
4°	5042.1
5°	4924.8
6°	4792.3
7°	4642.2
8°	4492.1
9°	4340.9
10°	4196.6
11°	4055.9
12°	3923.4
13°	3800.3
14°	3677.2
15°	3562.3
16°	3449.7
17°	3338.3
18°	3230.4
19°	3121.4
20°	3014.7
21°	2908.0
22°	2806.0
23°	2705.1
24°	2601.9
25°	2498.8
26°	2392.1
27°	2276.0
28°	2154.0
29°	2020.3
30°	1876.1
32.5°	1471.6
35°	1035.4
37.5°	682.4
40°	446.8
42.5°	308.4
45°	213.4
47.5°	146.6
50°	97.3
52.5°	63.3
55°	42.2
57.5°	28.1
60°	18.8
62.5°	12.9
65°	9.4



TEST NUMBER: P244367

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	5.9
70°	3.5
72.5°	2.3
75°	2.3
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)