

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246622

Luminaire Tested: **LD8B40D010 ER8B40835 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40835 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4052.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246622

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246622

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131033
5°	130094
10°	118550
15°	101614
20°	90055
25°	80362
30°	64900
35°	45030
40°	28572
45°	21225
50°	18115
55°	15881
60°	14209
65°	12696
70°	10945
75°	10068
80°	9376
85°	8279



TEST NUMBER: P246622

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.7	9.6
10°-20°	896.6	22.1
20°-30°	1066.2	26.3
30°-40°	753.8	18.6
40°-50°	389.1	9.6
50°-60°	266.7	6.6
60°-70°	173.1	4.3
70°-80°	90.8	2.2
80°-90°	27.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2350.5	58.0
0°-40°	3104.3	76.6
0°-60°	3760.1	92.8
0°-90°	4052.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4052.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4249	
5°	4203	388
15°	3183	897
25°	2362	1066
35°	1196	754
45°	487	389
55°	295	267
65°	174	173
75°	84	91
85°	23	26
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246622

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4249.3
2.5°	4249.3
5°	4202.8
7.5°	4048.2
10°	3786.1
12.5°	3473.5
15°	3183.0
17.5°	2944.0
20°	2744.3
22.5°	2555.4
25°	2361.9
27.5°	2119.0
30°	1822.7
32.5°	1503.9
35°	1196.2
37.5°	921.6
40°	709.8
42.5°	571.2
45°	486.7
47.5°	425.3
50°	377.6
52.5°	335.8
55°	295.4
57.5°	259.8
60°	230.4
62.5°	199.7
65°	174.0
67.5°	150.8
70°	121.4
72.5°	104.3
75°	84.5
77.5°	68.6
80°	52.8
82.5°	39.3
85°	23.4
87.5°	13.5
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246622

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)