

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245332

Luminaire Tested: **LD8B40D010 ER8B40840 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40840 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4883.0 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245332

CATALOG NUMBER: LD8B40D010 ER8B40840 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245332

CATALOG NUMBER: LD8B40D010 ER8B40840 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85287
5°	85613
10°	86690
15°	88385
20°	89648
25°	90018
30°	87258
35°	79644
40°	68895
45°	54237
50°	34987
55°	17171
60°	7062
65°	3094
70°	893
75°	334
80°	249
85°	0



TEST NUMBER: P245332

CATALOG NUMBER: LD8B40D010 ER8B40840 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.1	5.4
10°-20°	782.4	16.0
20°-30°	1211.4	24.8
30°-40°	1312.3	26.9
40°-50°	944.4	19.3
50°-60°	316.0	6.5
60°-70°	47.8	1.0
70°-80°	4.1	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2257.9	46.2
0°-40°	3570.3	73.1
0°-60°	4830.6	98.9
0°-90°	4883.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4883.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2766	
5°	2766	264
15°	2769	782
25°	2646	1211
35°	2116	1312
45°	1244	944
55°	319	316
65°	42	48
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P245332

CATALOG NUMBER: LD8B40D010 ER8B40840 8LBS0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2765.8
2.5°	2765.8
5°	2765.8
7.5°	2767.2
10°	2768.6
12.5°	2771.4
15°	2768.6
17.5°	2757.3
20°	2731.9
22.5°	2693.7
25°	2645.7
27.5°	2569.3
30°	2450.6
32.5°	2295.2
35°	2115.7
37.5°	1922.1
40°	1711.5
42.5°	1485.4
45°	1243.7
47.5°	982.2
50°	729.3
52.5°	500.3
55°	319.4
57.5°	190.8
60°	114.5
62.5°	69.3
65°	42.4
67.5°	21.2
70°	9.9
72.5°	4.2
75°	2.8
77.5°	2.8
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)