

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244085

Luminaire Tested: **LD8B50D010 ER8B509730 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B509730 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4572.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244085
CATALOG NUMBER: LD8B50D010 ER8B509730 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244085

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244085

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBSOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.8	5.3
10°-20°	728.1	15.9
20°-30°	1128.0	24.7
30°-40°	1225.0	26.8
40°-50°	890.1	19.5
50°-60°	302.5	6.6
60°-70°	48.2	1.1
70°-80°	5.2	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2099.9	45.9
0°-40°	3324.9	72.7
0°-60°	4517.6	98.8
0°-90°	4572.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4572.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2549	
5°	2550	244
15°	2577	728
25°	2463	1128
35°	1975	1225
45°	1172	890
55°	308	303
65°	42	48
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P244085

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2549.1
2.5°	2549.1
5°	2550.5
7.5°	2554.4
10°	2562.3
12.5°	2571.4
15°	2576.7
17.5°	2571.4
20°	2550.5
22.5°	2512.4
25°	2462.6
27.5°	2387.9
30°	2280.3
32.5°	2137.4
35°	1974.8
37.5°	1797.8
40°	1605.0
42.5°	1396.5
45°	1172.3
47.5°	931.0
50°	691.0
52.5°	473.4
55°	308.2
57.5°	187.5
60°	112.8
62.5°	69.5
65°	42.0
67.5°	23.6
70°	10.5
72.5°	6.6
75°	3.9
77.5°	2.6
80°	2.6
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

(END OF REPORT)