

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243869

Luminaire Tested: **LD8B50D010 ER8B509730 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B509730 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4279.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243869

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243869

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P243869

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.9	5.8
10°-20°	818.0	19.1
20°-30°	1287.0	30.1
30°-40°	1224.2	28.6
40°-50°	564.4	13.2
50°-60°	128.2	3.0
60°-70°	8.4	0.2
70°-80°	1.7	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2351.8	55.0
0°-40°	3576.1	83.6
0°-60°	4268.7	99.8
0°-90°	4279.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4279.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2462	
5°	2525	247
15°	2902	818
25°	2823	1287
35°	2007	1224
45°	691	564
55°	124	128
65°	6	8
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P243869

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2462.0
1°	2460.8
2°	2465.5
3°	2479.6
4°	2500.6
5°	2525.2
6°	2555.7
7°	2588.4
8°	2622.4
9°	2662.2
10°	2704.3
11°	2746.5
12°	2791.0
13°	2833.1
14°	2871.8
15°	2902.2
16°	2924.4
17°	2939.7
18°	2946.7
19°	2945.5
20°	2937.3
21°	2923.3
22°	2905.7
23°	2882.3
24°	2855.4
25°	2822.6
26°	2783.9
27°	2734.8
28°	2676.2
29°	2608.3
30°	2529.9
32.5°	2294.6
35°	2006.6
37.5°	1671.8
40°	1306.5
42.5°	965.8
45°	690.7
47.5°	489.4
50°	337.2
52.5°	215.4
55°	124.1
57.5°	62.0
60°	26.9
62.5°	10.5
65°	5.9



TEST NUMBER: P243869

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	3.5
70°	2.3
72.5°	2.3
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)