

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251438

Luminaire Tested: **LD8B60D010 ER8B60827 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60827 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5388.0 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251438

CATALOG NUMBER: LD8B60D010 ER8B60827 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251438

CATALOG NUMBER: LD8B60D010 ER8B60827 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174234
5°	172987
10°	157640
15°	135119
20°	119750
25°	106856
30°	86300
35°	59877
40°	37992
45°	28219
50°	24087
55°	21118
60°	18896
65°	16884
70°	14552
75°	13380
80°	12466
85°	11003



TEST NUMBER: P251438

CATALOG NUMBER: LD8B60D010 ER8B60827 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.5	9.6
10°-20°	1192.2	22.1
20°-30°	1417.8	26.3
30°-40°	1002.3	18.6
40°-50°	517.4	9.6
50°-60°	354.7	6.6
60°-70°	230.2	4.3
70°-80°	120.7	2.2
80°-90°	37.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3125.5	58.0
0°-40°	4127.8	76.6
0°-60°	4999.9	92.8
0°-90°	5388.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5388.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5650	
5°	5588	515
15°	4232	1192
25°	3141	1418
35°	1591	1002
45°	647	517
55°	393	355
65°	231	230
75°	112	121
85°	31	35
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251438

CATALOG NUMBER: LD8B60D010 ER8B60827 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5650.3
2.5°	5650.3
5°	5588.5
7.5°	5383.0
10°	5034.5
12.5°	4618.7
15°	4232.5
17.5°	3914.7
20°	3649.2
22.5°	3398.0
25°	3140.6
27.5°	2817.7
30°	2423.7
32.5°	1999.7
35°	1590.6
37.5°	1225.5
40°	943.8
42.5°	759.5
45°	647.1
47.5°	565.6
50°	502.1
52.5°	446.5
55°	392.8
57.5°	345.5
60°	306.4
62.5°	265.5
65°	231.4
67.5°	200.5
70°	161.4
72.5°	138.6
75°	112.3
77.5°	91.2
80°	70.2
82.5°	52.3
85°	31.1
87.5°	18.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251438

CATALOG NUMBER: LD8B60D010 ER8B60827 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)