

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244906

Luminaire Tested: **LD8B40D010 ER8B40850 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244906  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B40D010 ER8B40850 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4791.0 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244906

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244906

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	83764
5°	83505
10°	82755
15°	81936
20°	81054
25°	79773
30°	77583
35°	74050
40°	68625
45°	57943
50°	39750
55°	21924
60°	11021
65°	6202
70°	3381
75°	2407
80°	1527
85°	1026



TEST NUMBER: P244906

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	255.7	5.3
10°-20°	723.8	15.1
20°-30°	1077.6	22.5
30°-40°	1224.2	25.6
40°-50°	1000.6	20.9
50°-60°	392.1	8.2
60°-70°	91.4	1.9
70°-80°	22.0	0.5
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2057.2	42.9
0°-40°	3281.3	68.5
0°-60°	4674.1	97.6
0°-90°	4791.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4791.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2716	
5°	2698	256
15°	2567	724
25°	2345	1078
35°	1967	1224
45°	1329	1001
55°	408	392
65°	85	91
75°	20	22
85°	3	4
90°	0	



TEST NUMBER: P244906

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2716.4
2.5°	2712.1
5°	2697.7
7.5°	2673.2
10°	2642.9
12.5°	2605.5
15°	2566.6
17.5°	2520.4
20°	2470.0
22.5°	2410.9
25°	2344.6
27.5°	2266.8
30°	2178.9
32.5°	2079.5
35°	1967.1
37.5°	1843.1
40°	1704.8
42.5°	1537.6
45°	1328.7
47.5°	1083.7
50°	828.6
52.5°	595.2
55°	407.8
57.5°	266.6
60°	178.7
62.5°	122.5
65°	85.0
67.5°	56.2
70°	37.5
72.5°	25.9
75°	20.2
77.5°	14.4
80°	8.6
82.5°	4.3
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)