

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251154

Luminaire Tested: **LD8B60D010 ER8B60830 8LBM0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251154  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B60D010 ER8B60830 8LBM0WH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6088.0 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251154

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBM0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251154

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBM0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	235667
5°	240191
10°	229007
15°	202210
20°	175234
25°	148066
30°	111271
35°	74505
40°	41723
45°	16759
50°	5805
55°	1607
60°	913
65°	795
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251154

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBM0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	726.0	11.9
10°-20°	1766.7	29.0
20°-30°	1960.5	32.2
30°-40°	1242.1	20.4
40°-50°	344.6	5.7
50°-60°	39.5	0.6
60°-70°	7.7	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4453.3	73.1
0°-40°	5695.3	93.5
0°-60°	6079.4	99.9
0°-90°	6088.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6088.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7642	
5°	7760	726
15°	6334	1767
25°	4352	1961
35°	1979	1242
45°	384	345
55°	30	39
65°	11	8
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251154

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBM0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7642.5
2.5°	7699.0
5°	7759.6
7.5°	7638.6
10°	7313.7
12.5°	6850.3
15°	6334.1
17.5°	5827.2
20°	5340.0
22.5°	4861.8
25°	4351.8
27.5°	3755.4
30°	3125.0
32.5°	2514.4
35°	1979.2
37.5°	1495.6
40°	1036.5
42.5°	644.6
45°	384.3
47.5°	221.0
50°	121.0
52.5°	59.2
55°	29.9
57.5°	22.5
60°	14.8
62.5°	7.8
65°	10.9
67.5°	5.4
70°	0.0
72.5°	1.6
75°	0.0
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251154

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBM0WH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)