

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250818

Luminaire Tested: **LD8B60D010 ER8B60830 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60830 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5718.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250818

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250818

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	863861
5°	599996
10°	315732
15°	199765
20°	148457
25°	116713
30°	84028
35°	36059
40°	12567
45°	4819
50°	1118
55°	419
60°	0
65°	569
70°	171
75°	465
80°	693
85°	0



TEST NUMBER: P250818

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1554.0	27.2
10°-20°	1805.5	31.6
20°-30°	1558.3	27.3
30°-40°	676.0	11.8
40°-50°	106.0	1.9
50°-60°	7.7	0.1
60°-70°	4.1	0.1
70°-80°	4.3	0.1
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4917.8	86.0
0°-40°	5593.8	97.8
0°-60°	5707.4	99.8
0°-90°	5718.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5718.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	28014	
5°	19383	###
15°	6258	1806
25°	3430	1558
35°	958	676
45°	110	106
55°	8	8
65°	8	4
75°	4	4
85°	0	2
90°	0	



TEST NUMBER: P250818

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	28014.4
2.5°	25297.7
5°	19383.4
7.5°	13824.0
10°	10083.4
12.5°	7737.1
15°	6257.5
17.5°	5262.8
20°	4524.0
22.5°	3893.7
25°	3430.3
27.5°	2941.6
30°	2359.9
32.5°	1640.5
35°	957.9
37.5°	535.2
40°	312.2
42.5°	193.9
45°	110.5
47.5°	89.2
50°	23.3
52.5°	11.6
55°	7.8
57.5°	3.9
60°	0.0
62.5°	1.9
65°	7.8
67.5°	5.8
70°	1.9
72.5°	9.7
75°	3.9
77.5°	0.0
80°	3.9
82.5°	1.9
85°	0.0
87.5°	3.9
90°	0.0

(END OF REPORT)