

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251440

Luminaire Tested: **LD8B60D010 ER8B60830 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251440
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60830 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5523.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251440

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251440

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178601
5°	177321
10°	161589
15°	138503
20°	122749
25°	109534
30°	88461
35°	61375
40°	38942
45°	28930
50°	24692
55°	21644
60°	19371
65°	17307
70°	14912
75°	13713
80°	12786
85°	11286



TEST NUMBER: P251440

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	528.4	9.6
10°-20°	1222.1	22.1
20°-30°	1453.3	26.3
30°-40°	1027.4	18.6
40°-50°	530.3	9.6
50°-60°	363.6	6.6
60°-70°	236.0	4.3
70°-80°	123.8	2.2
80°-90°	38.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3203.8	58.0
0°-40°	4231.2	76.6
0°-60°	5125.1	92.8
0°-90°	5523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5523.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5792	
5°	5728	528
15°	4338	1222
25°	3219	1453
35°	1630	1027
45°	663	530
55°	403	364
65°	237	236
75°	115	124
85°	32	36
90°	0	3
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251440

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5791.9
2.5°	5791.9
5°	5728.5
7.5°	5517.9
10°	5160.6
12.5°	4734.5
15°	4338.5
17.5°	4012.8
20°	3740.6
22.5°	3483.2
25°	3219.3
27.5°	2888.3
30°	2484.4
32.5°	2049.8
35°	1630.4
37.5°	1256.2
40°	967.4
42.5°	778.5
45°	663.4
47.5°	579.7
50°	514.7
52.5°	457.7
55°	402.6
57.5°	354.2
60°	314.1
62.5°	272.2
65°	237.2
67.5°	205.5
70°	165.4
72.5°	142.1
75°	115.1
77.5°	93.5
80°	72.0
82.5°	53.6
85°	31.9
87.5°	18.4
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251440

CATALOG NUMBER: LD8B60D010 ER8B60830 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)