

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244372

Luminaire Tested: **LD8B40D010 ER8B40930 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40930 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3291.3 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244372

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244372

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244372

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	422.5	12.8
10°-20°	944.2	28.7
20°-30°	1073.5	32.6
30°-40°	630.4	19.2
40°-50°	169.2	5.1
50°-60°	40.2	1.2
60°-70°	9.2	0.3
70°-80°	2.0	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2440.1	74.1
0°-40°	3070.6	93.3
0°-60°	3279.9	99.7
0°-90°	3291.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3291.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5024	
5°	4668	422
15°	3377	944
25°	2369	1073
35°	981	630
45°	202	169
55°	40	40
65°	9	9
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P244372

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5024.1
1°	4996.3
2°	4945.2
3°	4873.0
4°	4779.6
5°	4668.4
6°	4542.9
7°	4400.6
8°	4258.2
9°	4114.9
10°	3978.2
11°	3844.8
12°	3719.1
13°	3602.4
14°	3485.7
15°	3376.8
16°	3270.2
17°	3164.6
18°	3062.2
19°	2958.9
20°	2857.8
21°	2756.7
22°	2659.9
23°	2564.3
24°	2466.5
25°	2368.7
26°	2267.6
27°	2157.5
28°	2041.9
29°	1915.2
30°	1778.5
32.5°	1395.0
35°	981.4
37.5°	646.9
40°	423.5
42.5°	292.4
45°	202.3
47.5°	138.9
50°	92.3
52.5°	60.0
55°	40.0
57.5°	26.7
60°	17.8
62.5°	12.2
65°	8.9



TEST NUMBER: P244372

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	5.6
70°	3.4
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)