

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250844

Luminaire Tested: **LD8B60D010 ER8B60835 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60835 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6469.9 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250844

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250844

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	348043
5°	333085
10°	296531
15°	238218
20°	186578
25°	150645
30°	116733
35°	66487
40°	25078
45°	10815
50°	4351
55°	1624
60°	870
65°	591
70°	361
75°	238
80°	0
85°	0



TEST NUMBER: P250844

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	987.7	15.3
10°-20°	2072.1	32.0
20°-30°	2027.7	31.3
30°-40°	1121.8	17.3
40°-50°	217.1	3.4
50°-60°	33.3	0.5
60°-70°	8.2	0.1
70°-80°	2.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5087.4	78.6
0°-40°	6209.2	96.0
0°-60°	6459.6	99.8
0°-90°	6469.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6469.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11287	
5°	10761	988
15°	7462	2072
25°	4428	2028
35°	1766	1122
45°	248	217
55°	30	33
65°	8	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P250844

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11286.8
2.5°	11131.6
5°	10760.6
7.5°	10240.4
10°	9470.2
12.5°	8496.4
15°	7462.0
17.5°	6492.2
20°	5685.7
22.5°	5018.4
25°	4427.6
27.5°	3871.1
30°	3278.4
32.5°	2582.8
35°	1766.2
37.5°	1062.5
40°	623.0
42.5°	389.1
45°	248.0
47.5°	155.2
50°	90.7
52.5°	50.4
55°	30.2
57.5°	18.1
60°	14.1
62.5°	10.1
65°	8.1
67.5°	6.0
70°	4.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)