

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245788

Luminaire Tested: **LD8B40D010 ER8B40935 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40935 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3717.0 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245788

CATALOG NUMBER: LD8B40D010 ER8B40935 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245788

CATALOG NUMBER: LD8B40D010 ER8B40935 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65792
5°	65592
10°	64944
15°	64279
20°	63606
25°	62564
30°	60852
35°	58081
40°	54001
45°	45593
50°	30957
55°	16171
60°	7259
65°	3539
70°	1425
75°	870
80°	639
85°	425



TEST NUMBER: P245788

CATALOG NUMBER: LD8B40D010 ER8B40935 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.8	5.4
10°-20°	567.9	15.3
20°-30°	845.4	22.7
30°-40°	961.1	25.9
40°-50°	785.9	21.1
50°-60°	292.9	7.9
60°-70°	53.6	1.4
70°-80°	8.3	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1614.2	43.4
0°-40°	2575.2	69.3
0°-60°	3654.0	98.3
0°-90°	3717.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3717.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2134	
5°	2119	201
15°	2014	568
25°	1839	845
35°	1543	961
45°	1046	786
55°	301	293
65°	48	54
75°	7	8
85°	1	1
90°	0	



TEST NUMBER: P245788

CATALOG NUMBER: LD8B40D010 ER8B40935 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2133.6
2.5°	2129.9
5°	2119.0
7.5°	2099.6
10°	2074.1
12.5°	2045.0
15°	2013.5
17.5°	1977.1
20°	1938.3
22.5°	1892.2
25°	1838.8
27.5°	1778.2
30°	1709.0
32.5°	1630.2
35°	1542.9
37.5°	1449.5
40°	1341.5
42.5°	1208.1
45°	1045.5
47.5°	850.3
50°	645.3
52.5°	454.9
55°	300.8
57.5°	189.2
60°	117.7
62.5°	75.2
65°	48.5
67.5°	27.9
70°	15.8
72.5°	9.7
75°	7.3
77.5°	4.9
80°	3.6
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)