

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250820

Luminaire Tested: **LD8B60D010 ER8B60835 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250820
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60835 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5945.9 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250820

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250820

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	898305
5°	623920
10°	328322
15°	207730
20°	154373
25°	121367
30°	87379
35°	37497
40°	13066
45°	5011
50°	1161
55°	435
60°	0
65°	591
70°	180
75°	477
80°	710
85°	0



TEST NUMBER: P250820

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1615.9	27.2
10°-20°	1877.5	31.6
20°-30°	1620.4	27.3
30°-40°	703.0	11.8
40°-50°	110.2	1.9
50°-60°	8.0	0.1
60°-70°	4.3	0.1
70°-80°	4.5	0.1
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5113.9	86.0
0°-40°	5816.8	97.8
0°-60°	5935.0	99.8
0°-90°	5945.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5945.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	29131	
5°	20156	###
15°	6507	1877
25°	3567	1620
35°	996	703
45°	115	110
55°	8	8
65°	8	4
75°	4	4
85°	0	2
90°	0	



TEST NUMBER: P250820

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	29131.4
2.5°	26306.4
5°	20156.3
7.5°	14375.2
10°	10485.5
12.5°	8045.6
15°	6507.0
17.5°	5472.6
20°	4704.3
22.5°	4049.0
25°	3567.1
27.5°	3058.9
30°	2454.0
32.5°	1705.9
35°	996.1
37.5°	556.5
40°	324.6
42.5°	201.6
45°	114.9
47.5°	92.8
50°	24.2
52.5°	12.1
55°	8.1
57.5°	4.0
60°	0.0
62.5°	2.0
65°	8.1
67.5°	6.0
70°	2.0
72.5°	10.1
75°	4.0
77.5°	0.0
80°	4.0
82.5°	2.0
85°	0.0
87.5°	4.0
90°	0.0

(END OF REPORT)